



Table 8 • Printer Parameters (Sheet 4 of 22)

Language/Parameter	Action/Explanation														
	<p><b>Set Print Width</b></p> <p>This parameter specifies the printable area across the width of the label. Table 9 shows the ranges and default values for print width, which are based on the printer model and the printhead resolution.</p> <p style="text-align: center;"><b>Table 9 • Print Width Ranges and Maximum Values</b></p> <table border="1" data-bbox="581 531 1422 915"> <thead> <tr> <th data-bbox="581 531 760 642" rowspan="2">Printhead Resolution</th> <th colspan="2" data-bbox="764 531 1422 583">Printer</th> </tr> <tr> <th data-bbox="764 590 1089 642">110Xi4/R110Xi4</th> <th data-bbox="1094 590 1422 642">140Xi4, 170Xi4, 220Xi4</th> </tr> </thead> <tbody> <tr> <td data-bbox="581 648 760 737"><b>200 dpi</b></td> <td data-bbox="764 648 1089 737"><i>Default Value:</i> 832 <i>Range:</i> 2 to 832 dots</td> <td data-bbox="1094 648 1422 737"><i>Default Value:</i> 1344 <i>Range:</i> 2 to 1344 dots</td> </tr> <tr> <td data-bbox="581 743 760 831"><b>300 dpi</b></td> <td data-bbox="764 743 1089 831"><i>Default Value:</i> 1248 <i>Range:</i> 2 to 1248 dots</td> <td data-bbox="1094 743 1422 831"><i>Default Value:</i> 1984 <i>Range:</i> 2 to 1984 dots</td> </tr> <tr> <td data-bbox="581 837 760 915"><b>600 dpi</b></td> <td data-bbox="764 837 1089 915"><i>Default Value:</i> 2496 <i>Range:</i> 2 to 2496 dots</td> <td data-bbox="1094 837 1422 915">N/A</td> </tr> </tbody> </table> <p> <b>Note</b> • Setting the width too narrow can result in portions of a label format not being printed on the media. Setting the width too wide wastes formatting memory and can cause printing off of the label and on the platen roller. This setting can affect the horizontal position of the label format if the image was inverted using the ^POI ZPL II command.</p> <p><b>To change the value shown:</b></p> <ol style="list-style-type: none"> <li>1. Press PLUS (+) or MINUS (-) to change the value shown.</li> </ol>	Printhead Resolution	Printer		110Xi4/R110Xi4	140Xi4, 170Xi4, 220Xi4	<b>200 dpi</b>	<i>Default Value:</i> 832 <i>Range:</i> 2 to 832 dots	<i>Default Value:</i> 1344 <i>Range:</i> 2 to 1344 dots	<b>300 dpi</b>	<i>Default Value:</i> 1248 <i>Range:</i> 2 to 1248 dots	<i>Default Value:</i> 1984 <i>Range:</i> 2 to 1984 dots	<b>600 dpi</b>	<i>Default Value:</i> 2496 <i>Range:</i> 2 to 2496 dots	N/A
Printhead Resolution	Printer														
	110Xi4/R110Xi4	140Xi4, 170Xi4, 220Xi4													
<b>200 dpi</b>	<i>Default Value:</i> 832 <i>Range:</i> 2 to 832 dots	<i>Default Value:</i> 1344 <i>Range:</i> 2 to 1344 dots													
<b>300 dpi</b>	<i>Default Value:</i> 1248 <i>Range:</i> 2 to 1248 dots	<i>Default Value:</i> 1984 <i>Range:</i> 2 to 1984 dots													
<b>600 dpi</b>	<i>Default Value:</i> 2496 <i>Range:</i> 2 to 2496 dots	N/A													